

NEW

Industrial Water Treatment



GENERATION

**New high-performance gel-type
cation exchange resins**

Lewatit MonoPlus[®] S 108

Lewatit MonoPlus[®] S 108 H

LANXESS
Energizing Chemistry

X LEWATIT[®]
ION EXCHANGE RESINS

LEWATIT MONOPLUS® S 108* AND LEWATIT MONOPLUS® S 108 H* – NEW MULTI-TALENTED PRODUCTS

■ Proven monodispersity and improved stability

The special monodisperse ion exchange matrix helps to ensure long service life even with low cycle times (regeneration/exhaustion). One of the key properties of Lewatit MonoPlus® S 108 and S 108 H is that the resin beads remain in excellent condition even after many exhaustion cycles. Thanks to the beads' improved chemical and physical stability, there is a much lower risk of problems occurring due to fines. The formation of such fines is virtually negligible due to the high level of monodispersity in production (uniformity coefficient ≤ 1.05).

■ Higher capacity

To increase economic efficiency, the functionality of the resins has been improved. A higher "total capacity" helps to ensure high operating capacities with very low leakage and low regenerant requirement. The degree of crosslinking achieved with Lewatit MonoPlus® S 108 (H) ensures outstanding kinetics.

		Total capacity
Lewatit MonoPlus® S 108	eq/l	min. 2.2
Lewatit MonoPlus® S 108 H	eq/l	min. 2.0

■ Minimum self-leaching and high oxidation stability


On account of the latest measuring techniques, the leaching behavior of cation exchange resins has become an important quality characteristic. Self-leaching or oxidation attack (e.g. through free chlorine) can result in the additional generation of high molecular weight substances. Lewatit MonoPlus® S 108 and S 108 H have very low self-leaching characteristics, and their chemical matrix has improved resistance to oxidation attack. The graph on the right shows the relationship between storage time in weeks and extinction (self-leaching). A high level of extinction leads to a marked increase in the release of TOC (total organic carbon) from the cation exchanger, which can, in turn, result in blocking of the anion ex-changer. The operating conditions in the unit deteriorate and the quality of the water produced is reduced.

■ Optimized use in mixed beds


One of the most critical operations in mixed bed polisher systems is the separation and regeneration (internal or external) step of ion exchange resins. A perfect separation of the both ion exchange components is essential, both physically and visually. The use of Lewatit MonoPlus® S 108 or Lewatit MonoPlus® S 108 H with a monodispersity resulting in an uniformity coefficient of max. 1.05 is next to an appropriate difference in resin density and sharply contrasting colours one of the dominating factors in order to reach both, excellent separation behaviour and required regeneration efficiency. Lewatit MonoPlus® S 108 and Lewatit MonoPlus® S 108 H are the results of more than 50 years of experience in the development and production of ion exchange resins. Both resins are optimally geared to use with other Lewatit® products.

Contact


LANXESS Sybron Chemicals Inc | 200 Birmingham Road | Birmingham
 NJ 8011 | Tel.: Toll Free 800678-0020 | Fax: 609 726 0049
www.lewatit.com | lewatit.northamerica@lanxess.com




Stability of a competitive product after the osmotic shock test



Stability of Lewatit MonoPlus® S 108 H after the osmotic shock test



Operating capacity of the cation exchange resin (H-form) compared with that of competitive products



TOC release (leaching) of the cation exchange resin (H-form) compared with that of competitive products



Perfect separation of cation and anion exchange resins in a mixed bed

The manner in which you use and the purpose to which you put and utilize our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations are beyond our control. Therefore, it is imperative that you test our products, technical assistance and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us. Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale. All information and technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed that you assume and hereby expressly release us from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent.

* Patent pending